

Konverteringsliste mellem DTIP og DEViflex

El. nr.	DTIP-15
72 35 861 606	DEVIFLEX DTIP-15 8M, 120W 230V
72 35 861 619	DEVIFLEX DTIP-15 16M, 255W 230V
72 35 861 622	DEVIFLEX DTIP-15 24M, 360W 230V
72 35 861 635	DEVIFLEX DTIP-15 32M, 485W 230V
72 35 861 648	DEVIFLEX DTIP-15 40M, 630W 230V
72 35 861 651	DEVIFLEX DTIP-15 47M, 740W 230V
72 35 861 664	DEVIFLEX DTIP-15 56M, 865W 230V
72 35 861 677	DEVIFLEX DTIP-15 73M, 1135W 230V
72 35 861 693	DEVIFLEX DTIP-15 89M, 1370W 230V
72 35 861 716	DEVIFLEX DTIP-15 113M, 1745W 230V
72 35 861 732	DEVIFLEX DTIP-15 127M, 1985W 230V
72 35 861 745	DEVIFLEX DTIP-15 143M, 2215W 230V



El. nr.	DEViflex 18T
72 35 870 503	DEViflex 18T 130W 230V 7.3m
72 35 870 532	DEViflex 18T 270W 230V 15m
72 35 870 558	DEViflex 18T 395W 230V 22m
7 235 870 561	DEViflex 18T 535W 230V 29m
72 35 870 587	DEViflex 18T 680W 230V 37m
72 35 870 590	DEViflex 18T 820W 230V 44m
72 35 870 600	DEViflex 18T 935W 230V 52m
7 23 5870 626	DEViflex 18T 1220W 230V 68m
72 35 870 639	DEViflex 18T 1340W 230V 74m
72 35 870 668	DEViflex 18T 1880W 230V 105m
72 35 870 671	DEViflex 18T 2135W 230V 118m
72 35 870 684	DEViflex 18T 2420W 230V 131m

El. nr.	DTIP-10
72 35 866 229	DEVIFLEX DTIP-10 2M, 20W 230V
72 35 866 232	DEVIFLEX DTIP-10 4M, 40W 230V
72 35 866 245	DEVIFLEX DTIP-10 6M, 60W 230V
72 35 866 258	DEVIFLEX DTIP-10 8M, 80W 230V
72 35 866 261	DEVIFLEX DTIP-10 10M, 100W 230V
72 35 866 274	DEVIFLEX DTIP-10 15M, 135W 230V
72 35 866 287	DEVIFLEX DTIP-10 20M, 200W 230V
72 35 866 290	DEVIFLEX DTIP-10 25M, 240W 230V
72 35 866 300	DEVIFLEX DTIP-10 30M, 300W 230V
72 35 866 313	DEVIFLEX DTIP-10 35M, 350W 230V
72 35 866 326	DEVIFLEX DTIP-10 40M, 400W 230V
72 35 866 339	DEVIFLEX DTIP-10 50M, 500W 230V
72 35 866 342	DEVIFLEX DTIP-10 60M, 600W 230V
72 35 866 355	DEVIFLEX DTIP-10 70M, 700W 230V
72 35 866 368	DEVIFLEX DTIP-10 80M, 800W 230V
72 35 866 371	DEVIFLEX DTIP-10 90M, 900W 230V
72 35 866 384	DEVIFLEX DTIP-10 100M, 1000W 230V
72 35 866 397	DEVIFLEX DTIP-10 120M, 1200W 230V
72 35 866 407	DEVIFLEX DTIP-10 140M, 1400W 230V
72 35 866 410	DEVIFLEX DTIP-10 160M, 1600W 230V
72 35 866 423	DEVIFLEX DTIP-10 180M, 1800W 230V
72 35 866 436	DEVIFLEX DTIP-10 200M, 2000W 230V
72 35 866 449	DEVIFLEX DTIP-10 210M, 2100W 230V



El. nr.	DEViflex 10T
72 35 870 202	DEViflex 10T 20W 230V 2m
72 35 870 215	DEViflex 10T 40W 230V 4m
72 35 870 228	DEViflex 10T 60W 230V 6m
72 35 870 231	DEViflex 10T 80W 230V 8m
72 35 870 244	DEViflex 10T 100W 230V 10m
72 35 870 257	DEViflex 10T 135W 230V 15m
72 35 870 260	DEViflex 10T 205W 230V 20m
72 35 870 273	DEViflex 10T 240W 230V 25m
72 35 870 286	DEViflex 10T 290W 230V 30m
72 35 870 299	DEViflex 10T 350W 230V 35m
72 35 870 309	DEViflex 10T 390W 230V 40m
72 35 870 312	DEViflex 10T 505W 230V 50m
72 35 870 325	DEViflex 10T 600W 230V 60m
72 35 870 338	DEViflex 10T 695W 230V 70m
72 35 870 341	DEViflex 10T 790W 230V 80m
72 35 870 354	DEViflex 10T 920W 230V 90m
72 35 870 367	DEViflex 10T 990W 230V 100m
72 35 870 370	DEViflex 10T 1220W 230V 120m
72 35 870 383	DEViflex 10T 1410W 230V 140m
72 35 870 396	DEViflex 10T 1575W 230V 160m
72 35 870 406	DEViflex 10T 1760W 230V 180m
72 35 870 419	DEViflex 10T 1990W 230V 200m
72 35 870 422	DEViflex 10T 2050W 230V 210m

El. nr.	DTIP-6
72 35 868 010	Deviflex DTIP-6 180W 230V 30m
72 35 868 023	Deviflex DTIP-6 250W 230V 40m
72 35 868 036	Deviflex DTIP-6 310W 230V 50m
72 35 868 049	Deviflex DTIP-6 345W 230V 60m
72 35 868 052	Deviflex DTIP-6 415W 230V 70m
72 35 868 065	Deviflex DTIP-6 500W 230V 80m
72 35 868 078	Deviflex DTIP-6 540W 230V 90m
72 35 868 081	Deviflex DTIP-6 635W 230V 100m
72 35 868 094	Deviflex DTIP-6 690W 230V 110m
72 35 868 104	Deviflex DTIP-6 765W 230V 125m
72 35 868 117	Deviflex DTIP-6 870W 230V 140m
72 35 868 120	Deviflex DTIP-6 915W 230V 160m
72 35 868 133	Deviflex DTIP-6 1095W 230V 180m
72 35 868 146	Deviflex DTIP-6 1160W 230V 190m
72 35 868 159	Deviflex DTIP-6 1260W 230V 200m



El. nr.	DEViflex 6T
72 35 870 008	DEViflex 6T 180W 230V 30m
72 35 870 011	DEViflex 6T 250W 230V 40m
72 35 870 024	DEViflex 6T 310W 230V 50m
72 35 870 037	DEViflex 6T 345W 230V 60m
72 35 870 040	DEViflex 6T 415W 230V 70m
72 35 870 053	DEViflex 6T 500W 230V 80m
72 35 870 066	DEViflex 6T 540W 230V 90m
72 35 870 079	DEViflex 6T 635W 230V 100m
72 35 870 082	DEViflex 6T 660W 230V 115m
72 35 870 095	DEViflex 6T 770W 230V 129m
72 35 870 105	DEViflex 6T 870W 230V 140m
72 35 870 118	DEViflex 6T 915W 230V 160m
72 35 870 121	DEViflex 6T 1095W 230V 180m
72 35 870 134	DEViflex 6T 1160W 230V 190m
72 35 870 147	DEViflex 6T 1260W 230V 200m